



Scattering Meter Calibration Sheet

5/15/2017

Wavelength: 700

S/N FLBBCDSL-4728

Use the following equation to obtain either digital or analog "scaled" output values:

$$\beta(\theta_c) \text{ m}^{-1} \text{ sr}^{-1} = \text{Scale Factor} \times (\text{Output} - \text{Dark Counts})$$

• Scale Factor for 700 nm	=	1.622E-06 (m ⁻¹ sr ⁻¹)/counts
• Output	=	meter output counts
• Dark Counts	=	41 counts
Instrument Resolution	=	1.0 counts

Definitions:

- **Scale Factor:** Calibration scale factor, $\beta(\theta_c)/\text{counts}$. Refer to User's Guide for derivation.
 - **Output:** Measured signal output of the scattering meter.
 - **Dark Counts:** Signal obtained by covering detector with black tape and submersing sensor in water.
- Instrument Resolution: Standard deviation of 1 minute of collected data.